

По вопросам продаж и поддержки обращайтесь:

Алматы (7273)495-231  
Ангарск (3955)60-70-56  
Архангельск (8182)63-90-72  
Астрахань (8512)99-46-04  
Барнаул (3852)73-04-60  
Белгород (4722)40-23-64  
Благовещенск (4162)22-76-07  
Брянск (4832)59-03-52  
Владивосток (423)249-28-31  
Владикавказ (8672)28-90-48  
Владимир (4922)49-43-18  
Волгоград (844)278-03-48  
Вологда (8172)26-41-59  
Воронеж (473)204-51-73  
Екатеринбург (343)384-55-89  
Иваново (4932)77-34-06  
Ижевск (3412)26-03-58  
Иркутск (395)279-98-46  
Казань (843)206-01-48

Калининград (4012)72-03-81  
Калуга (4842)92-23-67  
Кемерово (3842)65-04-62  
Киров (8332)68-02-04  
Коломна (4966)23-41-49  
Кострома (4942)77-07-48  
Краснодар (861)203-40-90  
Красноярск (391)204-63-61  
Курган (3522)50-90-47  
Курск (4712)77-13-04  
Липецк (4742)52-20-81  
Магнитогорск (3519)55-03-13  
Москва (495)268-04-70  
Мурманск (8152)59-64-93  
Набережные Челны (8552)20-53-41  
Нижний Новгород (831)429-08-12  
Новокузнецк (3843)20-46-81  
Новосибирск (383)227-86-73  
Ноябрьск(3496)41-32-12

Омск (3812)21-46-40  
Орел (4862)44-53-42  
Оренбург (3532)37-68-04  
Пенза (8412)22-31-16  
Пермь (342)205-81-47  
Петрозаводск (8142)55-98-37  
Псков (8112)59-10-37  
Ростов-на-Дону (863)308-18-15  
Рязань (4912)46-61-64  
Самара (846)206-03-16  
Санкт-Петербург (812)309-46-40  
Саранск (8342)22-96-24  
Саратов (845)249-38-78  
Севастополь (8692)22-31-93  
Симферополь (3652)67-13-56  
Смоленск (4812)29-41-54  
Сочи (862)225-72-31  
Ставрополь (8652)20-65-13  
Сургут (3462)77-98-35

Сыктывкар (8212)25-95-17  
Тамбов (4752)50-40-97  
Тверь (4822)63-31-35  
Тольятти (8482)63-91-07  
Томск (3822)98-41-53  
Тула (4872)33-79-87  
Тюмень (3452)66-21-18  
Улан-Удэ (3012)59-97-51  
Ульяновск (8422)24-23-59  
Уфа (347)229-48-12  
Хабаровск (4212)92-98-04  
Чебоксары (8352)28-53-07  
Челябинск (351)202-03-61  
Череповец (8202)49-02-64  
Чита (3022)38-34-83  
Якутск (4112)23-90-97  
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +7(7172)727-132

Киргизия +996(312)96-26-47

<https://gea.nt-rt.ru/> || [gsg@nt-rt.ru](mailto:gsg@nt-rt.ru)

# ГОМОГЕНИЗАТОРЫ XSTREAM LAB

## Технические характеристики



# Smart, simple and safe

## Best performance thanks to the NiSoX-Valve

With an innovative ergonomic geometry and design, this table top unit is dedicated to facilitate the testing and scaling of the NiSoX-Valve benefits in various applications while ensuring safe, smart and easy operating conditions.

GEA homogenization experts engineered the concept in

order to guarantee a high reliability machine that extends the lifetime of components and gives the opportunity to test great performances of the innovative NiSoX-Valve.

The new XStream is the ideal homogenizer to carry out tests

in laboratory and be prepared to scale up to the industrial production thanks to the consistent results that NiSoX-Valve provides for many and different applications.

## Optimized high quality efficiency with 100% trials repeatability thanks to automation

The enhanced level of automation adds several benefits for an easy use of the machine:

- Improved performance on the product
- Saving of energy and resources
- Improved responsiveness (up to 2000 bar in about 5 sec.)
- Minimized product loss
- Easy reproduction and scalability of test results
- Easy validation process

## Main features

- Designed to fit the standard laboratory desk size
- Improved operation speed with PLC and HMI touchscreen 7"
- Optimized pressure regulation with automatic set-up for constant operating

Thanks to the self adjustment pressure regulation, this special user friendly configuration simplifies the maintenance procedures while reducing significantly human errors.

The automated features ensure better process stability and machine operation efficiency.

## Main options available

The new lab unit is available in two models: XStream Lab Homogenizer 1000 and 2000 with different options according to specific requirements and Pharma execution:

- cGMP, CFR21 and GAMP certifications with data recorder
- Frequency converter for variable flow-rate (external)
- Mini compressor for pneumatic circuit (external)
- Collar sensors for inlet and outlet temperature
- Heat exchanger
- Larger feeding hopper (2l)
- Jacked feeding hopper and pneumatic pusher